











Example: Wi-Fi



Belden offers a full suite of copper and fiber cable and connectivity systems that support every type of technology you'll need – now and in the future. Learn more about how Belden is uniquely positioned to provide reliable products and services for your wireless jobs. Visit www.belden.com/wireless.

	Description	Belden Part Number
 Fiber Cables	FX Indoor OS2 Distribution Tight Buffer, 6f OFNP, Yellow Jacket	FISD006P9
	FX Indoor/Outdoor OS2 Distribution Tight Buffer, 6f OFNP, Black Jacket	FSD006P9
	FX Indoor OS2 Distribution Tight Buffer, 6f OFCP, AIA, Yellow Jacket	FISD006A9
	FX Indoor/Outdoor OS2 Distribution Tight Buffer, 6f OFCP, AIA, Black Jacket	FSD006A9
 Pigtails	FX Fusion Splicer Kit	FXFSTOSPL
	FX Field-Term Pigtail, OS2, LC/APC Simplex, Tight Buffer, 900 µm, 12f, 2 m	FTSLB900PR12
	FX Field-Term Pigtail, OS2, SC/APC Simplex, Tight Buffer, 900 µm, 12f, 2 m	FTSSB900PR12
	Heat Shrink Protector Sleeves, 900 µm to 900 µm, 2.5 mm dia x 60 mm, 25pcs	FXFUHS900AB25
 Patch Cords	FX Patch Cord, OS2, LC/APC Duplex - LC/APC Duplex, 2M, A-TO-B	FPSLALA002M
	FX Patch Cord, OS2, SC/APC Duplex - SC/APC Duplex, 2M, A-TO-B	FPSSASA002M
	FX Patch Cord, OS2, LC/APC Duplex - SC/APC Duplex, 2M, A-TO-B	FPSLASA002M
 Patch Panels	FX ECX 1U Patch Panel Housing	ECX-01U
	FX ECX 2U Patch Panel Housing	ECX-02U
	FX ECX 4U Patch Panel Housing	ECX-04U
	FX ECX 4U Rack-Mounting Bracket, Flush	ECX-BRKTMT-0
	FX ECX Door Lock Kit	ECX-LOCKKIT
 Cassettes	FX ECX Splice Cassette, OS2, LC/APC Duplex, 6 Port, 12f, Green	FCSX06LAFS
	FX ECX Splice Cassette, OS2, LC/APC Duplex, 12 Port, 24f, Green	FCSX12LAFS
	FX ECX Splice Cassette, OS2, SC/APC Duplex, 3 Port, 6f, Green	FCSX03SAFS
	FX ECX Splice Cassette, OS2, SC/APC Duplex, 6 Port, 12f, Green	FCSX06SAFS
 Wall-Mount Boxes	FX ECX Single Cassette Holder	ECX-01WH
 Digital Electricity™ Cables	DE Copper Only 16 AWG, 2 Cu Pairs, Plenum	DEIP162U
	DE Copper Only 18 AWG, 2 Cu Pairs, Plenum	DEIP182U
	DE Hybrid, 16 AWG, 2 Cu Pairs, 6f, OS2, Distribution, 4.5 mm Sub, Plenum	DHIP162USD06J
	DE Hybrid, 18 AWG, 2 Cu Pairs, 6f, OS2, Distribution, 4.5 mm Sub, Plenum	DHIP182USD06J
 Coaxial Cables	1/2" Air Plenum Coax, Corrugated Copper; Blue, 1000 ft Reel	RA500P 0061000
	1/2" Air Plenum Coax, Corrugated Copper; Off-White, 1000 ft Reel	RA500P 3651000
	1/2" Low Loss, Corrugated Copper, Riser Rated Coax, Black, 1000 ft Reel	RA500R 0101000
 Racks and Managers	Four-Post Distribution Rack	XDR8419-3122836
	Two-Post Distribution Rack	XDR8419-310N
	Horizontal Manager	BHH 191 UR
	Vertical Manager	BHV H003